





			
111 ★★★★★ ■●○ Titanium white	113 ★★★★★ ▣●○ Buff titanium light	115 ★★★★★ ■ Mineral white	221 ★★★★★ ■●○ Ivory	222 ★★★★★ ▣● Lemon yellow	223 ★★★★★ ▣● Cadmium yellow hue
					
224 ★★★★★ ▣●○ Primary yellow	225 ★★★★★ ▣● Chrome yellow hue	226 ★★★ □●○ Indian yellow	227 ★★★★★ ▣● Cadmium orange hue	228 ★★★ ▣● Cadmium yellow hue deep	230 ★★★ ▣● Orange
					
331 ★★★★★ ■ Flesh colour	333 ★★★ ▣●○ Vermilion red	335 ★★★ ■ Cadmium red hue	340 ★★★ ▣● Carmine red	341 ★★★ ▣● Cadmium red hue dark	343 ★★★★★ □● Alizarin crimson hue
					
344 ★★★★★ ▣●○ Primary magenta	348 ★★★★★ ■ Lilac	440 ★★★★★ □●○ Brilliant violet	441 ★★★★★ ■● Royal blue	442 ★★★★★ ▣●○ Ultramarine blue	443 ★★★★★ ■● Cobalt blue hue deep
					
444 ★★★★★ ■● Indigo	446 ★★★★★ ▣●○ Primary blue cyan	447 ★★★★★ ▣● Prussian blue	448 ★★★★★ □ Phthalo blue	449 ★★★★★ ■● Cerulean blue	450 ★★★★★ ▣● Turquoise
					
551 ★★★★★ □● Phthalo green	552 ★★★★★ ▣● Leaf green	553 ★★★★★ □ Phthalo green light	554 ★★★★★ ■ Permanent green	557 ★★★★★ ▣●○ May green	558 ★★★★★ ■ Olive green
					
560 ★★★ ▣● Sap green	655 ★★★★★ ▣● Raw Siena	656 ★★★★★ ■ Raw umber light	657 ★★★★★ ■ Pebble grey	659 ★★★★★ ▣● Naples yellow	660 ★★★★★ ■● Buff titanium deep
					
661 ★★★★★ ■● Yellow ochre	662 ★★★★★ ■ Flesh tint	663 ★★★★★ ■● Terracotta	665 ★★★★★ ■ Burnt Sienna	667 ★★★★★ ■ Raw umber	668 ★★★★★ ▣●○ Vandyke brown
					
669 ★★★★★ ▣● Burnt umber	658 ★★★★★ ■ Payne's grey	770 ★★★★★ ■ Mars black	771 ★★★★★ ■●○ Lamp black	800 ★★★★★ ■● Silver	801 ★★★★★ ▣● Gold
					
802 ★★★★★ ■ Copper	806 ★★★★★ ■ Graphite	840 □ Fluorescent white	845 ▣● Neon yellow	850 ▣● Neon orange	855 ▣● Neon pink

Classification symbols

- ★★★★★ extremely lightfast
- ★★★★ good lightfastness
- ★★★ lightfast
- ★★ limited lightfastness
- ★ less lightfast

- transparent
- ▣ semi-transparent
- ▣ semi-opaque
- opaque

60 colours –  60 ml

60 colours –  250 ml

60 colours –  120 ml

36 colours –  500 ml

12 colours ○ – 2,5 Liter

